


Bedienungsanleitung, Ausdrehen der weichen Spanneinsätze SW




Aufbau

- Lagerbolzen herausdrehen.
- Pendelbrücke entfernen.
- O-Ring durch Scheibe \varnothing 16.7 x 5 ersetzen.
 - ✓ Durch die Scheibe wird die Lage der Pendelbrücke fixiert.
- Passscheibe zwischen Lagerbolzen und Pendelbrücke einsetzen.
 - ✓ Durch die Passscheibe wird Pendelbrücke geklemmt.
- Nach dem Ausdrehen, Umbau rückgängig machen.

Ausdrehsatz (bestehend aus 3x Passscheibe und 3x Fixierscheibe)

Größe der Pendelbacken	Identnummer
\varnothing 200	1320458
\varnothing 250 - 315	1320463
\varnothing 400 und größer	1320464

Operating manual, Turning out of the soft pendulum jaws



Configuration

- Unscrew pivot bolt.
- Remove pendulum body.
- Exchange O-ring against disc Ø 16.7 x 5.
 - ✓ The position of the pendulum body is fixed by means of the disk.
- Insert fitting disc between pivot bolt and the pendulum body.
 - ✓ The pendulum body is locked by the means of the fitting disc
- After turning out, reverse the conversion.

Turning out sets (consisting of 3x fitting disc and 3x fixing disc)

Size of pendulum jaw	Ident number
Ø 200	1320458
Ø 250 - 315	1320463
Ø 400 and above	1320464