



Superior Clamping and Gripping



T|E|N|D|O® E compact
**The Hydraulic Expansion
Toolholder**

Secure your price advantage by
ordering a starter kit at £299.00 now

TENDO® E compact Hydraulic Expansion toolholder

Starter-Kit

TENDO® E compact

The universal hydraulic expansion toolholder for volume cutting, boring, reaming and thread-cutting.

Tighter tolerances, huge cost pressure, better quality – TENDO E compact is the answer to increasing demands in volume cutting – demands which can no longer be met economically using ER collets, heat shrink toolholders, Weldon toolholders and cheap hydraulic expansion toolholders.

The TENDO E compact boasts a price which makes it easier to change from mechanical and thermal toolholders to significantly higher-precision TENDO quality.

- Maximum clamping torque now up to 900 Nm with \varnothing 20 mm under dry clamping conditions, 520 Nm with oily tool shanks
- Permanent run-out and repeat accuracy of less than 0.003 mm
- For universal use in milling, boring, reaming and thread-cutting
- Increases service life of tools by up to 40% leading to cost savings
- Tool changes in seconds with no peripheral equipment – clamping to a dead stop



* This campaign is only valid in the UK as long as stock lasts, or until further notice. All prices are subject to value added tax at the statutory rate currently amounting to 20%.

Secure your price advantage!

The TENDO E compact starter kit contains:

- 1 x TENDO E compact (either HSK-A63 \varnothing 20, SK40 \varnothing 20 or BT40 \varnothing 20)
- 5 x GZB-S \varnothing 20 (with clamping \varnothing 6, \varnothing 8, \varnothing 10, \varnothing 12, \varnothing 16) coolant proof up to max. 80 bar
- 1 x sleeve remover
- 1 x actuating key
- 1 x exclusive packaging

TENDO E compact	HSK-A 63	SK 40	BT 40
Part number	0299970	0299969	0299968
Total price	£495.00	£485.00	£485.00
You save	£196.00	£186.00	£186.00

Special-offer price*	£299.00	£299.00	£299.00
-----------------------------	----------------	----------------	----------------

T | E | N | D | O® E compact

The toolholder for almost every requirement

TENDO E compact is setting completely new standards. A strong performance during torque transmission, damping characteristics, rigidity and run-out accuracy, the TENDO E compact is perfect for precise and fast metal cutting – even for roughing applications.

1 Volume machining

TENDO E compact is the first hydraulic expansion toolholder, which is suitable for volume machining e.g. 400 cm³/min (25 in³/min) with 42CrM04 (4140)*. *depending on the machine tool and the cutting tool

2 Reaming

During reaming the excellent vibration damping assures best workpiece surfaces and a permanent run-out accuracy for an excellent dimensional accuracy.

3 Drilling




Drilling – the classic strength of the TENDO-family. Vibration damping and a run-out accuracy of less than 0.003 mm are the main strengths of the TENDO E compact.

4 Countersinking/Chamfering

By using TENDO E compact countersinking and chamfering are defined by precision and excellent run-out accuracy.

5 Tapping

At high torques (of up to 900 Nm at \varnothing 20 mm) and excellent vibration damping, the TENDO E compact was made for tapping.



The T|E|N|D|O® E compact –Starter-Kit

Fax order – complete and fax to

+44-1908-615525



TENDO E compact	HSK-A 63	SK 40	BT 40
Part number	0299970	0299969	0299968
Total price	£495.00	£485.00	£485.00
You save	£196.00	£188.00	£188.00

Special-offer Price* £299.00 £299.00 £299.00

* This campaign is only valid in the UK as long as stock lasts, or until further notice. All prices are subject to value added tax at the statutory rate currently amounting to 20%.

- Please call me
- Yes, I want to subscribe to the monthly SCHUNK newsletter.

Name _____ Customer number _____

Company _____ Department _____

Street _____

Postcode _____ City _____

Telephone _____ Fax _____

E-Mail _____

Date _____

Signature _____



J. Lehmann

Jens Lehmann, German goalkeeper legend, brand ambassador for SCHUNK, the family-owned company, since 2012
www.gb.schunk.com/Lehmann